



Main

Product or component type	Power socket-outlet
Switch function	Switch
Rated current	13 A, 250 V, , AC, 50...60 Hz
Number of gangs	1 gang
Load type	Resistive
Cover frame colour tint	Lavender silver


Complementary

Wiring device mounting	Flush Surface
Material	Polycarbonate with grid plate Polycarbonate with surround
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 2 x 4 mm ² for stranded cable(s)
Width	87 mm
Height	87 mm
Depth	26.6 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	BS 1363-2 SS 145-2 MS 589-2

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1110 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**