



Main

Product or component type	Fused connection unit
Rated current	13 A, 250 V, AC, 50 Hz
Switch function	2-pole
Bulb type	Neon
Load type	Resistive
Protection type	Fuse
Number of gangs	1 gang
Cover frame colour tint	White

Complementary

Wiring device mounting	Flush Surface
Material	Polycarbonate with grid plate Polycarbonate with surround
Clamping connection capacity	2 x 4 mm ² for stranded cable(s) 1 x 2.5 mm ² for solid cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	33.2 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	BS 1363

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**