

# Product data sheet

## Characteristics

# E8233DMWS\_WE

16AX 3G SW w Ne w "Privacy", "Pls Clean Up"  
& "Pls Wait " Sym, White



### Main

Range	Pieno
Product or component type	Switch
Switch application	Control switch
Load type	Fluorescent Resistive
Cover frame colour tint	White

### Complementary

Wiring device mounting	Surface Flush
Device mounting	Surface Flush
Switch function	Switch
Rated current	16 AX at 250 V AC 50 Hz
Local signalling	Please wait, neon (orange) Please clean up, neon (green) Privacy, neon (red)
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - terminals	By screw
Width	25.3 Mm
Height	76.5 Mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	MS IEC 60669-1 SS 227-1 IEC 60669-1 GB 16915.1 BS EN 60669-1

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**