



### Main

Range	AvatarOn
Product or component type	Switched socket
Device application	Power supply
Device presentation	Complete product
Outlet poles configuration	3P with shutter
Colour tint	Metal gold hairline
Type of packing	Flow-pack

### Complementary

Rated current	15 A socket-outlet
[Ue] rated operational voltage	250 V AC 50/60 Hz
Socket number	1
Outlet standard description	With earthing contact
Outlet standard	China
Pilot light	LED
Service life in cycles	20000 Cycles
Electrical durability	5000 Cycles
Connections - terminals	Screw terminal
Material	Polycarbonate: grid plate Polycarbonate: surround
Surface finish	Glossy
Surface treatment	Painted mechanism cover
Device mounting	Surface
Fixing mode	Screw
Height	86 Mm
Width	86 Mm
Depth	32.6 Mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

IP degree of protection	IP20
Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	-5...60 °C
Standards	SS 472 BS 546 MS 1577
Product certifications	SIRIM

Product Life Status : **Commercialised**