



Main

Range	AvatarOn
Product or component type	Cover plate
Accessory / separate part category	Mounting accessory
Colour tint	Light wood painted
Type of packing	Flow-pack





Complementary

Range compatibility	Switch
Product destination	Switch
Number of rocker	3
Material	PC (polycarbonate)
Surface finish	Glossy
Surface treatment	Untreated
Height	86 Mm
Width	86 Mm
Depth	21 Mm

Environment

Ambient air temperature for storage	-5...45 °C
Ambient air temperature for operation	0...95 °C
Standards	IEC 60670 BS 5733

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Environmental Disclosure

 [Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations

Product Life Status :	Commercialised
-----------------------	-----------------------