

Product data sheet

Characteristics

E8415-10USN_SZ

10A 1 Gang Switched 2 Universal+3 Flat Pin
Socket w/ Shutter&Neon, Silver Bronze



Main

Product or component type	Power socket-outlet
Socket additional information	Shuttered
Outlet poles configuration	2P + E China 2P universal
Load type	Resistive
Cover frame colour tint	Silver bronze
Cover plate colour tint	Bronze

Complementary

Device mounting	Flush Surface
Local signalling	Indicator light, neon (amber)
Rated current	10 A at 250 V AC 50 Hz
Number of gangs	1 gang
Material	Polycarbonate grid plate Polycarbonate surround
Connections - terminals	Clamps terminal
Embedding depth	20.1 Mm
Width	87 Mm
Height	87 Mm
Depth	27 Mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	GB 2099.1 GB 16915.1
Standards	GB 16915.1 GB 2099.1

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**