

## Product data sheet

### Characteristics

# E8415DEN\_SA

13A 1 Gang Double Pole Switched Socket w/  
Neon&Dual Earth Terminal, Silver Satin



### Commercial status

End of Commercialisation :

⚠ End of Commercialisation

### Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P + E
Load type	Resistive
Cover frame colour tint	Silver satin
Cover plate colour tint	Grey

### Complementary

Device mounting	Flush Surface
Local signalling	Indicator light, neon (amber)
Rated current	13 A at 250 V AC 50 Hz
Number of gangs	1 gang
Material	Polycarbonate base Polycarbonate grid plate Polycarbonate surround
Connections - terminals	Folded terminal
Width	87 Mm
Height	87 Mm
Depth	8 Mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	BS 1363-2 MS 589 SS 145
Standards	SS 145 BS 1363-2 MS 589

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. - Block**