

Main

Product or component type	Power socket-outlet
Load type	Resistive
Cover frame colour tint	Silver bronze
Cover plate colour tint	Bronze

Complementary

Device mounting	Flush Surface
Local signalling	Mechanical indicator amber
Switch function	2-pole
Rated current	13 A 250 V AC 50 Hz
Number of gangs	1 gang
Material	Brass contact Phosphor contact Polycarbonate base Polycarbonate grid plate Polycarbonate surround
Connections - terminals	Folded terminal
Width	87 mm
Height	87 mm
Depth	8 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	BS 1363-2 MS 589 SS 145
Standards	MS 589 SS 145 BS 1363-2

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**