



Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P china
Load type	Resistive
Colour tint	White
Cover frame colour tint	White

Complementary

Device mounting	Surface Flush
Local signalling	Mechanical indicator red
Rated current	10 A 250 V AC 50 Hz
Number of gangs	1 gang
Material	Brass contact plate Bronze contact plate Polycarbonate grid plate Polycarbonate surround
Connections - terminals	Clamps terminal
Width	87 mm
Height	87 mm
Depth	27 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	GB 16915.1 IEC 60884-2-3 GB 2099.1
Standards	IEC 60884-2-3 GB 16915.1 GB 2099.1

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**