

Main

Range	ZENcelo
Product or component type	Power socket-outlet
Socket additional information	Shuttered
Outlet poles configuration	2P + E China
Load type	Resistive
Colour tint	Wine gold
Cover frame colour tint	White



Complementary

Device mounting	Surface Flush
Rated current	16 A at 250 V AC 50 Hz
Number of gangs	1 gang
Material	Polycarbonate grid plate Polycarbonate surround Brass contact plate
Connections - terminals	Clamps terminal
Embedding depth	17.8 Mm
Width	87 Mm
Height	87 Mm
Depth	27 Mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Product Life Status : **Commercialised**