

## Product data sheet

### Characteristics

# E8431BPDM\_SZ

1 Gang Bell Switch w/Illuminated  
"DoNotDisturb&PleaseCleanUp" Sym., Silver  
Bronze



### Main

Range	ZENcelo
Product or component type	Switch
Device application	Bell switch
Load type	Inductive lamp Resistive
Colour tint	Silver bronze
Cover frame colour tint	Silver bronze

### Complementary

Device mounting	Flush Surface
Number of gangs	1 gang
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	27.72 mm

### Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	BS EN 60669-1 GB 16915.1 IEC 60669-1 MS IEC 60669-1

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.