



Main

Range	ZENcelo
Product or component type	Switch
Device application	Bell switch
Load type	Inductive lamp Resistive
Colour tint	Silver satin
Cover frame colour tint	Silver satin

Complementary

Device mounting	Surface Flush
Rated current	10 A at 250 V AC 50/60 Hz
Local signalling	Do not disturb: indicator light, neon (orange)
Number of gangs	1 gang
Material	Brass: contact Polycarbonate: base Polycarbonate: cover Polycarbonate: grid plate Polycarbonate: surround
Connections - terminals	Pillar terminals
Width	87 Mm
Height	87 Mm
Depth	27.72 Mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	BS EN 60669-1 GB 16915.1 MS IEC 60669-1 IEC 60669-1

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------