

### Main

|                           |                             |
|---------------------------|-----------------------------|
| Range                     | ZENcelo                     |
| Product or component type | Switch                      |
| Device application        | Bell switch                 |
| Load type                 | Inductive lamp<br>Resistive |
| Colour tint               | Silver white                |
| Cover frame colour tint   | Silver white                |

### Complementary

|                         |                  |
|-------------------------|------------------|
| Device mounting         | Flush<br>Surface |
| Number of gangs         | 1 gang           |
| Connections - terminals | Pillar terminals |
| Width                   | 87 mm            |
| Height                  | 87 mm            |
| Depth                   | 27.72 mm         |

### Environment

|                                       |  |
|---------------------------------------|--|
| Ambient air temperature for operation | -5...35 °C   |
| Relative humidity                     | 0...95 %   |
| Environmental characteristic          | No UV resistant  |
| Operating altitude                    | 2000 m   |
| Standards                             | BS EN 60669-1<br>GB 16915.1<br>IEC 60669-1<br>MS IEC 60669-1 |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Product Life Status : **Commercialised**