



### Main

Range	ZENcelo
Product or component type	Switch
Device application	Bell switch
Load type	Resistive Inductive lamp
Colour tint	White
Cover frame colour tint	White


### Complementary

Device mounting	Surface Flush
Rated current	10 A at 250 V AC 50/60 Hz
Local signalling	Do not disturb: indicator light, neon (orange)
Number of gangs	1 gang
Material	Brass: contact Polycarbonate: base Polycarbonate: cover Polycarbonate: grid plate Polycarbonate: surround
Connections - terminals	Pillar terminals
Width	87 Mm
Height	87 Mm
Depth	27.72 Mm

### Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	BS EN 60669-1 GB 16915.1 IEC 60669-1 MS IEC 60669-1

### Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------