



Main

Range	ZENcelo
Product or component type	Switch
Device application	Bell switch
Load type	Inductive lamp Resistive
Colour tint	White
Cover frame colour tint	White

Complementary

Device mounting	Flush Surface
Number of gangs	1 gang
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	27.72 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	BS EN 60669-1 GB 16915.1 IEC 60669-1 MS IEC 60669-1

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**