

Product data sheet

Characteristics

E8431D20_SA

20A 1 Gang Full-Flat Double Pole Switch with Neon, Silver Satin



Main

Range	ZENcelo
Product or component type	Switch
Load type	Inductive
Colour tint	Silver satin
Cover frame colour tint	Silver satin

Complementary

Device mounting	Surface Flush
Number of gangs	1 gang
Connections - terminals	Brass rod terminals
Embedding depth	23 mm
Width	87 mm
Height	87 mm
Depth	31.5 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Standards	GB 16915.1 BS EN 60669-1 IEC 60669-1 SS 227-1 MS IEC 60669-1

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1301 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.