

### Main

Range	ZENcelo
Product or component type	Switch
Load type	Inductive
Colour tint	White
Cover frame colour tint	White

### Complementary

Device mounting	Flush Surface
Number of gangs	1 gang
Connections - terminals	Brass rod terminals
Embedding depth	23 mm
Width	87 mm
Height	87 mm
Depth	31.5 mm

### Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Standards	BS EN 60669-1 GB 16915.1 IEC 60669-1 MS IEC 60669-1 SS 227-1

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**