



### Main

Range	ZENcelo
Product or component type	Switch
Load type	Fluorescent lamp Incandescent lamp Inductive
Colour tint	Silver satin
Cover frame colour tint	Silver satin

### Complementary

Device mounting	Surface Flush
Rated current	16 AX at 250 V AC 50/60 Hz
Local signalling	Do not disturb: indicator light, neon (amber) Please clean up: indicator light, neon (green)
Number of gangs	1 gang
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround
Connections - terminals	Brass rod terminals
Width	43.9 Mm
Height	50.7 Mm
Depth	1.8 Mm

### Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	GB 16915.1 MS IEC 60669-1 BS EN 60669-1 SS 227-1 IEC 60669-1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">Download RoHS China Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**