

Main

Range of product	ZENcelo
Product or component type	Dimmer
Local signalling	Indicator light LED amber on Indicator light LED blue off
Additional information	With memory push
[Ue] rated operational voltage	220...240 V AC 50 Hz
Material	Brass metal parts Polycarbonate plastic part Steel metal parts
Cover frame colour tint	Silver satin

Complementary

Wiring device mounting	Flush Surface
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 2 x 4 mm ² for stranded cable(s) 2 x 4 mm ² for solid cable(s)
Rated operational power in VA	350 VA
Number of gangs	1 gang
Load type	Incandescent lamp LV halogen
Embedding depth	6 mm
Width	87 mm
Height	87 mm
Depth	35 mm

Environment

Ambient air temperature for operation	<= 40 °C
Relative humidity	10...95 %
Ambient air temperature for storage	0...60 °C
Standards	IEC 60669-2-1

Offer Sustainability

RoHS (date code: YYWW)	Compliant  Schneider Electric Declaration Of Conformity
------------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	----------------