



Main

Range	ZENcelo
Product or component type	EMO switch


Complementary

Device mounting	Surface Flush
Cable cross section	1.5 mm ²
Rated current	3 A 24 V DC
Material	Polycarbonate
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	33.6 mm

Environment

Ambient air temperature for operation	<= 30 °C
Relative humidity	0...95 %

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1301 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.