

Product data sheet

Characteristics

E8432DMS_SZ

2 Gang Switch w/Illuminated
"DoNotDisturb&PleaseCleanUp" Symbols,
Silver Bronze



Main

| | |
|---------------------------|-----------------------------|
| Range | ZENcelo |
| Product or component type | Switch |
| Device application | Bell switch |
| Load type | Inductive lamp Resistive |
| Colour tint | Silver bronze |
| Cover frame colour tint | Silver bronze |

Complementary

| | |
|-------------------------|------------------|
| Device mounting | Flush Surface |
| Number of gangs | 2 gangs |
| Connections - terminals | Pillar terminals |
| Width | 87 mm |
| Height | 87 mm |
| Depth | 27.72 mm |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for operation | -5...35 °C |
| Relative humidity | 0...95 % |
| Environmental characteristic | No UV resistant |
| Operating altitude | 2000 m |
| Standards | BS EN 60669-1 GB 16915.1 IEC 60669-1 MS IEC 60669-1 |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.