



Main

Range	ZENcelo
Product or component type	Message indicator
Local signalling	Indicator light neon green please clean up Indicator light neon orange do not disturb
Colour tint	Silver bronze

Complementary

Device mounting	Flush Surface
Clamping connection capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
[Ue] rated operational voltage	250 V AC 50/60 Hz
Material	Brass contact Polycarbonate base Polycarbonate cover Polycarbonate grid plate Polycarbonate surround
Connections - terminals	Folded terminal illuminated indicators
Embedding depth	19.57 mm
Width	87 mm
Height	87 mm
Depth	27.72 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	<= 2000 m
Standards	EN 60669-1 GB 16915.1 IEC 60669-1 MS IEC 60669-1

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1301 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	----------------