



Main

Range	ZENcelo
Product or component type	Telephone socket
Socket additional information	Shuttered
Number of gangs	2 gangs
Material	PC for housing Polycarbonate for plastic part
Colour tint	Silver satin

Complementary

Device mounting	Surface Flush
Communication network category	3 voice
Rated current	1.5 A
Contacts material	Phosphor bronze with gold plating for contact Phosphor bronze with nickel plating for IDC contact
Contact resistance	$\leq 1 \mu\text{Ohm}$
Insulation resistance	$\geq 200 \text{ MOhm}$
Return loss	$\geq 23 \text{ dB}$
Width	87 mm
Height	87 mm
Depth	36 mm

Environment

Dielectric strength	1000 V for 60 s at 60 Hz
AWG gauge	AWG 26...AWG 22 4 twisted pair cables
Environmental characteristic	No UV resistant
Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Standards	TIA/EIA-568-B.2-1 ASTMD4566-98

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2016
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	----------------