

Main

Range	ZENcelo
Product or component type	Telephone socket
Socket additional information	Shuttered
Number of gangs	2 gangs
Material	PC for housing Polycarbonate for plastic part
Colour tint	Silver bronze

Complementary

Device mounting	Flush Surface
Communication network category	3 voice
Rated current	1.5 A
Contacts material	Phosphor bronze with gold plating for contact Phosphor bronze with nickel plating for IDC contact
Contact resistance	$\leq 1 \mu\text{Ohm}$
Insulation resistance	$\geq 200 \text{ MOhm}$
Return loss	$\geq 23 \text{ dB}$
Width	87 mm
Height	87 mm
Depth	36 mm

Environment

Dielectric strength	1000 V for 60 s at 60 Hz
AWG gauge	AWG 26...AWG 22 4 twisted pair cables
Environmental characteristic	No UV resistant
Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Standards	TIA/EIA-568-B.2-1 ASTMD4566-98

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant
REACH	Reference not containing SVHC above the threshold

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	----------------