

Product data sheet

Characteristics

E84426-10US_SA

10A 1 Gang 2 Universal Pin + 3 Flat Pin Socket with Shutter, Silver Satin



Main

Product or component type	Power socket-outlet
Socket additional information	Shuttered
Outlet poles configuration	2P + E China 2P universal
Load type	Resistive
Cover frame colour tint	Silver satin
Cover plate colour tint	Grey

Complementary

Device mounting	Flush Surface
Rated current	10 A at 250 V AC 50 Hz
Number of gangs	1 gang
Material	Polycarbonate grid plate Polycarbonate surround Brass contact plate Phosphor bronze contact plate
Connections - terminals	Clamps terminal
Embedding depth	17.8 Mm
Width	87 Mm
Height	87 Mm
Depth	27 Mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.