

Product data sheet

Characteristics

E84426-10US_SW

10A 1 Gang 2 Universal Pin + 3 Flat Pin Socket with Shutter, Silver White



Main

| | |
|-------------------------------|------------------------------|
| Product or component type | Power socket-outlet |
| Socket additional information | Shuttered |
| Outlet poles configuration | 2P + E China 2P universal |
| Load type | Resistive |
| Cover frame colour tint | Silver white |
| Cover plate colour tint | White |

Complementary

| | |
|-------------------------|--|
| Device mounting | Flush Surface |
| Rated current | 10 A at 250 V AC 50 Hz |
| Number of gangs | 1 gang |
| Material | Polycarbonate grid plate Polycarbonate surround Brass contact plate Phosphor bronze contact plate |
| Connections - terminals | Clamps terminal |
| Embedding depth | 17.8 Mm |
| Width | 87 Mm |
| Height | 87 Mm |
| Depth | 27 Mm |

Environment

| | |
|---------------------------------------|-----------------|
| Ambient air temperature for operation | -5...35 °C |
| Relative humidity | 0...95 % |
| Environmental characteristic | No UV resistant |
| Operating altitude | 2000 m |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.