

Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P
Load type	Resistive
Cover frame colour tint	Silver satin
Cover plate colour tint	Grey

Complementary

Device mounting	Flush Surface
Rated current	10 A 250 V AC 50 Hz
Number of gangs	2 gangs
Material	Brass contact plate Polycarbonate base Polycarbonate cover Polycarbonate grid plate Polycarbonate surround
Connections - terminals	Clamps terminal
Width	87 mm
Height	87 mm
Depth	27 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	IEC 60884-1 GB 2099.1
Standards	GB 2099.1 IEC 60884-1

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric Declaration Of Conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	----------------