



### Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P + E china
Load type	Resistive
Cover frame colour tint	Silver satin
Cover plate colour tint	Grey

### Complementary

Device mounting	Flush Surface
Rated current	10 A 250 V AC 50 Hz
Number of gangs	1 gang
Material	Bronze contact plate Polycarbonate base Polycarbonate cover Polycarbonate grid plate Polycarbonate surround
Connections - terminals	Clamps terminal
Width	87 mm
Height	87 mm
Depth	27 mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	IEC 60884-1 GB 2099.1
Standards	GB 2099.1 IEC 60884-1

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**