



Main

Range of product	ZENcelo
Range	ZENcelo
Product or component type	Power socket-outlet
Load type	No inductive load
Cover frame colour tint	Silver bronze
Cover plate colour tint	Bronze

Complementary

Device mounting	Flush Surface
Switch function	2-pole
Rated current	45 A 250 V AC 50 Hz
Number of gangs	1 gang
Material	Brass contact Phosphor contact Polycarbonate base Polycarbonate grid plate Polycarbonate surround control circuit
Connections - terminals	Folded terminal
Width	147 mm
Height	87 mm
Depth	8 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	BS 4177
Standards	BS 4177

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1809 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**