



Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P + E
Load type	Resistive
Cover frame colour tint	Silver white
Cover plate colour tint	White

Complementary

Device mounting	Flush Surface
Local signalling	Indicator light, neon (amber)
Rated current	13 A at 250 V AC 50 Hz
Number of gangs	2 gangs
Material	Brass contact Polycarbonate base Polycarbonate grid plate Polycarbonate surround Phosphor bronze contact
Connections - terminals	Folded terminal
Width	147 Mm
Height	87 Mm
Depth	8 Mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	BS 1363-2 MS 589 SS 145
Standards	MS 589 BS 1363-2 SS 145

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**