



### Commercial status

End of Commercialisation :

 End of Commercialisation

### Main

Product or component type	Power socket-outlet
Socket additional information	Shuttered
Outlet poles configuration	2P + E
Load type	Resistive
Cover frame colour tint	Silver white
Cover plate colour tint	White

### Complementary

Device mounting	Surface Flush
Rated current	16 A at 250 V AC 50 Hz
Number of gangs	2 gangs
Material	Polycarbonate base Polycarbonate grid plate Polycarbonate surround Polycarbonate cover Steel terminals
Connections - terminals	Clamps terminal
Embedding depth	29 Mm
Width	147 Mm
Height	87 Mm
Depth	40 Mm

### Environment

Ambient air temperature for operation	-5...25 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Operating altitude	2000 m
Standards	IEC 60884-1
Standards	IEC 60884-1

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. - Block**