



Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P + E
Load type	Resistive
Cover frame colour tint	Silver bronze
Cover plate colour tint	Bronze

Complementary

Device mounting	Flush Surface
Rated current	13 A 250 V AC 50 Hz
Number of gangs	2 gangs
Material	Brass contact Phosphor bronze contact Polycarbonate base Polycarbonate grid plate Polycarbonate surround
Connections - terminals	Folded terminal
Width	147 mm
Height	87 mm
Depth	8 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	BS 1363-2 MS 589 SS 145
Standards	MS 589 SS 145 BS 1363-2

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1809 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**