

Product data sheet

Characteristics

EJB34125AABA

E-Frame Brkr 125A, 3P, 480Y/277V, 65/100kA,
Bolt-on Mnt, Alarm/Aux SW



Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	125 A Frame EDB-EGB-EJB
Product or component type	Miniature circuit-breaker
Device short name	EJB
Module type	E-Frame
Trip unit rating	2300 A

Complementary

Line Rated Current	125 A
System Voltage	480Y/277 V AC
AWG gauge	AWG 12...AWG 2/0 aluminium AWG 14...AWG 2/0 copper
Breaking capacity	65 kA 277 V AC 65 kA 480Y/277 V AC 100 kA 120 V AC 100 kA 120/240 V AC 100 kA 240 V AC
Circuit breaker application	HACR rated
Depth	4.05 in
Electrical connection	Lugs aluminium
Height	5.66 in
Holding current	1000 A
Local signalling	Trip indicator
Mounting mode	Bolt-on
Number of poles	3
Number of spaces	4
Number of spaces required	4
Product destination	Panelboard NF
Product weight	4 lb(US)
Protection type	Short-circuit Overload

Width	3.92 in
Device composition	Alarm switch Auxiliary switch
Trip unit technology	Thermal-magnetic
Breaking capacity code	J

Environment

Product certifications	CULus
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	00937 - EJB CIRCUIT BREAKERS
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	4.299999999999998
Returnability	N
Country of origin	MX

Product Life Status :	Commercialised
-----------------------	----------------