



Main

Range of product	Mureva BOX
Product or component type	Junction box for security circuits
Colour tint	Red RAL 3000
Quantity per set	5 pieces

Complementary

Wiring device mounting	Surface
Cable entry	Grommets
Fixing mode	Screw-fixed cover
Base dimension	105 x 105 x 55 mm
Cable entry number	7 grommets Ø 25 mm
Material	PP (polypropylene) body and cover SBS (styrene butadiene styrene) grommet
Electrical insulation class	Class II according to IEC 536
Height	61 mm
Width	118 mm
Depth	118 mm
Product weight	0.131 kg

Environment

Ambient air temperature for operation	-25...40 °C
IP degree of protection	IP55 according to IEC 60529
IK degree of protection	IK07 according to EN 50102
Fire resistance	960 °C
Standards	EN 60670 CE
Environmental characteristic	Slightly halogenated

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1026 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	----------------