



Main

Range	Mureva
Product or component type	T-section
Colour tint	White
Quantity per set	25 pieces


Complementary

Accessory / separate part category	Installation accessory
Condition of use	Indoor/Outdoor
Material	PVC (polyvinyl chloride)
Crush resistance	750 N/m
Nominal cross section	119 mm ²
Internal diameter	21.3 mm
External diameter	25 mm
Product weight	0.042 kg

Environment

Ambient air temperature for operation	-5...60 °C
Quality labels	NF
Standards	EN 50086-2-1 EN 61386-21 : 2004
Environmental characteristic	Non-flame propagating
IP degree of protection	IP40
IK degree of protection	IK07

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1026 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**