



Main

Switch function	1-pole 2-way
Range	Asfora
Product or component type	Switch
Device presentation	Complete product
Load type	Load for energy saving lamps with ballast : 100 W
Colour tint	Anthracite
Type of packing	Flow-pack

Complementary

Number of rocker	1
Device mounting	Flush
Power range	2300 W
Rated current	10 AX 250 V AC
Connections - terminals	Screwless terminals
Number of cables	2 x 2.5 mm ²
Cable stiffness	Flexible Rigid Solid stranded
Wire stripping length	13 mm
Material	ABS (acrylonitrile butadiene-styrene)
Surface finish	Painted
Conductor material	Copper
Fixing mode	Screws or claws 51...70 mm
Height	83 mm
Width	83 mm
Depth	43 mm
Projecting depth	15 mm
Product weight	0.0858 kg

Environment

Standards	IEC 60669-1
Product certifications	NF TSE VDE
Quality labels	CE UKR
IP degree of protection	IP44
Ambient air temperature for operation	-5...40 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1809 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**