

Product data sheet

Characteristics

EZM3800FSB

EZM MAIN SWITCH 800A UG 3PHASE



Product availability: Stock - Normally stocked in distribution facility

Main

Range of product	EZ meter-pak
Product or component type	Meter center main unit
Main type	Main Fusible Switch
Provided equipment	Closing plate Main switch 3P 800 A 100 kA Interrupt Rating,

Complementary

Main rated current	800 A
Bus rated current	800 A
Material	Aluminium busbar
Enclosure material	Steel
System Voltage	208Y/120 V AC
Device mounting	Surface
Network number of phases	3 phases in 3 phases out
Service feed location	UG
Electrical connection	Lugs (1) cable(s) AWG 6...300 kcmil (aluminium/copper) ground Lugs (4) cable(s) AWG 3/0...500 kcmil (aluminium/copper) line Lugs (4) cable(s) AWG 3/0...500 kcmil (aluminium/copper) neutral
Wiring configuration	4-wire
Height	53.97 in
Width	18.66 in
Depth	11.5 in

Environment

Product certifications	UL listed
NEMA degree of protection	NEMA 3R

Ordering and shipping details

Category	00020 - EZ METER-PAK
Discount Schedule	DE4
GTIN	00785901821854
Nbr. of units in pkg.	1
Package weight(Lbs)	213
Returnability	N

Offer Sustainability

California proposition 65

WARNING: This product can expose you to chemicals including:

----- Substance 1

Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.

----- More information

For more information go to www.p65warnings.ca.gov

Product Life Status : **Commercialised**