

Product data sheet

Characteristics

FH26030CB

FA/LA MOLDED CASE CIRCUIT BREAKER

600V, 30A,



by Schneider Electric



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1456.80 USD

Main

| | |
|---------------------------|------------------|
| Product or component type | Circuit breaker |
| Range of product | I-Line |
| Trip unit technology | Thermal-magnetic |
| Breaking capacity code | H |

Complementary

| | |
|--------------------------------|--|
| Line Rated Current | 30 A |
| Poles description | 2P |
| Breaking capacity | 65 KA 240 V AC 10 KA 250 V DC 25 KA 480 V AC 18 KA 600 V AC |
| [Ue] rated operational voltage | 600 V AC 250 V DC |
| Mounting mode | I-Line |
| Electrical connection | Lugs load I-Line connection line |
| AWG gauge | AWG 14...AWG 4 copper)1 AWG 12...AWG 4 aluminium)1 |
| Terminal identifier | AL50FA |
| Magnetic hold current | 275 A |
| Magnetic tripping current | 600 A |
| Phase connection | CB |
| Maximum Height | 6.4 In (162.56 mm) |
| Width | 3 In (76.20 mm) |
| Depth | 4.13 In (104.90 mm) |

Environment

| | |
|------------------------|------------------|
| Product certifications | UL Listed CSA |
|------------------------|------------------|

Ordering and shipping details

| | |
|---------------------|-----------------------|
| Category | 01010 - FA/FH 600V |
| Discount Schedule | DE2 |
| GTIN | 00785901146032 |
| Package weight(Lbs) | 4.34 Lb(US) (1.97 kg) |
| Returnability | No |
| Country of origin | MX |

Offer Sustainability

| | |
|---------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: DIN-P, which is known to the State of California to cause cancer, and DID-P, which is known to the State of California to cause Birth Defects or other reproductive harm. For more information go to www.p65warnings.ca.gov |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **Commercialised**