

Product data sheet

Characteristics

FH26035BC

FA/LA MOLDED CASE CIRCUIT BREAKER

600V, 35A, 2P, 4PH



by Schneider Electric



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1456.80 USD

Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip unit technology	Thermal-magnetic
Breaking capacity code	H

Complementary

Line Rated Current	35 A
Poles description	2P
Breaking capacity	65 KA 240 V AC 10 KA 250 V DC 25 KA 480 V AC 18 KA 600 V AC
[Ue] rated operational voltage	600 V AC 250 V DC
Mounting mode	I-Line
Electrical connection	Lugs load I-Line connection line
AWG gauge	AWG 14...AWG 1/0 copper)1 AWG 12...AWG 1/0 aluminium)1
Terminal identifier	AL100FA
Magnetic hold current	400 A
Magnetic tripping current	850 A
Phase connection	BC
Maximum Height	6.4 In (162.56 mm)
Maximum Width	3 In (76.20 mm)
Maximum Depth	4.13 In (104.90 mm)

Environment

Product certifications	CSA UL Listed
------------------------	------------------

Ordering and shipping details

Category	01010 - FA/FH 600V
Discount Schedule	DE2
GTIN	00785901132325
Returnability	No
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DIN-P, which is known to the State of California to cause cancer, and DID-P, which is known to the State of California to cause Birth Defects or other reproductive harm.For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**