

# FHB16020A

## FA/LA MOLDED CASE CIRCUIT BREAKER

### 277V 20A



by Schneider Electric



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 730.80 USD



### Main

|                           |                  |
|---------------------------|------------------|
| Product or component type | Circuit breaker  |
| Range of product          | I-Line           |
| Trip unit technology      | Thermal-magnetic |
| Breaking capacity code    | H                |

### Complementary

|                                |   |
|--------------------------------|---|
| Line Rated Current             | 20 A  |
| Poles description              | 1P  |
| Breaking capacity              | 10 KA 125 V DC<br>65 KA 277 V AC                      |
| [Ue] rated operational voltage | 277 V AC<br>125 V DC                                  |
| Mounting mode                  | I-Line  |
| Electrical connection          | I-Line connection line<br>Bolted connection load      |
| AWG gauge                      | AWG 14...AWG 4 copper)1<br>AWG 12...AWG 4 aluminium)1 |
| Terminal identifier            | AL50FA  |
| Magnetic hold current          | 275 A   |
| Magnetic tripping current      | 600 A   |
| Maximum Height                 | 6.4 In (162.56 mm)                                    |
| Maximum Width                  | 1.5 In (38.10 mm)                                     |
| Maximum Depth                  | 4.13 In (104.90 mm)                                   |

### Environment

|                        |                  |
|------------------------|------------------|
| Product certifications | CSA<br>UL Listed |
|------------------------|------------------|

## Ordering and shipping details

|                     |                       |
|---------------------|-----------------------|
| Category            | 01010 - FA/FH 600V    |
| Discount Schedule   | DE2                   |
| GTIN                | 00785901338772        |
| Package weight(Lbs) | 2.55 Lb(US) (1.16 kg) |
| Returnability       | No                    |
| Country of origin   | MX                    |

## Offer Sustainability

|                           |   |
|---------------------------|---|
| Sustainable offer status  | Green Premium product   |
| California proposition 65 | WARNING: This product can expose you to chemicals including: DIN-P, which is known to the State of California to cause cancer, and DID-P, which is known to the State of California to cause Birth Defects or other reproductive harm.For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a> |
| EU RoHS Directive         | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>  |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **Commercialised**