

# FHB16020C

## FA/LA MOLDED CASE CIRCUIT BREAKER

### 277V 20A



by Schneider Electric



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 730.80 USD



### Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip unit technology	Thermal-magnetic
Breaking capacity code	H

### Complementary

Line Rated Current	20 A
Poles description	1P
Breaking capacity	10 KA 125 V DC 65 KA 277 V AC
[Ue] rated operational voltage	277 V AC 125 V DC
Mounting mode	I-Line
Electrical connection	I-Line connection line Bolted connection load
AWG gauge	AWG 14...AWG 4 copper)1 AWG 12...AWG 4 aluminium)1
Terminal identifier	AL50FA
Magnetic hold current	275 A
Magnetic tripping current	600 A
Maximum Height	6.4 In (162.56 mm)
Width	1.5 In (38.10 mm)
Depth	4.13 In (104.90 mm)

### Environment

Product certifications	UL Listed CSA
------------------------	------------------

## Ordering and shipping details

Category	01010 - FA/FH 600V
Discount Schedule	DE2
GTIN	00785901338796
Package weight(Lbs)	2.55 Lb(US) (1.16 kg)
Returnability	No
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DIN-P, which is known to the State of California to cause cancer, and DID-P, which is known to the State of California to cause Birth Defects or other reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**