

# Product data sheet

## Characteristics

# FHE36000AWK

## SWITCH FA/LA MOLDED CASE 3 POLE NEMA12



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1310.00 USD

### Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip unit technology	Thermal-magnetic
Breaking capacity code	H

### Complementary

Breaking capacity	10 KA 125 V DC 10 KA 250 V DC 25 KA 120/240 V AC 18 KA 277/480 V AC 14 KA 347/600 V AC
[Ue] rated operational voltage	600 V AC
Mounting mode	I-Line
Electrical connection	Lugs load I-Line connection line
AWG gauge	AWG 14...AWG 4 copper)1 AWG 12...AWG 4 aluminium)1
Terminal identifier	AL50FA
Magnetic hold current	275 A
Magnetic tripping current	600 A
Maximum Height	6 In (152.40 mm)
Maximum Width	4.5 In (114.30 mm)
Maximum Depth	4.13 In (104.90 mm)


### Environment

Product certifications	UL Listed CSA
------------------------	------------------

### Ordering and shipping details

Category	00066 - MISC H/D SWITCHES
Discount Schedule	DE1
GTIN	00785901076094
Package weight(Lbs)	17 Lb(US) (7.71 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: DINP and DIDP- which is known to the State of California to cause Carcinogen and Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
EU RoHS Directive	Will be compliant – Date to be confirmed
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	<b>Commercialised</b>
-----------------------	-----------------------