

Product data sheet

Characteristics

GS2AH410

External rotary handle, TeSys GS, black handle, front mounting, 2 positions I-O, NEMA 4-4X, for GS 30A Compact UL



Product availability: Stock - Normally stocked in distribution facility

Price*: 70.00 USD



Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AH
Product or component type	Rotary handle
Range compatibility	TeSys GS GS1D fuse-switch disconnecter
Type of operating handle	External frontal
Handle colour	Black
Handle front plate colour	Grey

Complementary

Marking	O-I
Rotary handle padlocking	With
Line Rated Current	30 A
Standards	UL CSA
Net weight	0.44 Lb(US) (0.2 kg)

Environment

NEMA degree of protection	NEMA 4/4X
---------------------------	-----------

Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901014386
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5 Lb(US) (0.23 kg)

Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.76 In (7 cm)
Package 1 width	4.72 In (12 cm)
Package 1 Length	5.51 In (14 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	20
Package 2 Weight	11.01 Lb(US) (4.996 kg)
Package 2 Height	11.81 In (30 cm)
Package 2 width	11.81 In (30 cm)
Package 2 Length	15.75 In (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**