



Main

| | |
|---------------------------|-------------------|
| Range of product | Ultimate |
| Range | Ultimate |
| Aesthetic name | Flat plate |
| Product or component type | Plate switch |
| Control type | Rocker |
| Switch function | 2-way retractive |
| Rated current | 16 AX at 230 V AC |

Complementary

| | |
|-------------------------|-----------------|
| Connections - terminals | Screw terminals |
| Material | Steel |
| Quantity per set | Set of 1 |
| Number of gangs | 1 gang |
| Device mounting | Wall mounted |
| Height | 88 Mm |
| Width | 88 Mm |
| Depth | 24 Mm |

Environment

| | |
|-------------------------|---------------|
| Standards | BS EN 60669-1 |
| IP degree of protection | IP20 |

Offer Sustainability

| | |
|----------------------------|---|
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **Commercialised**