



Main

| | |
|---------------------------|-------------------|
| Range of product | Ultimate |
| Range | Ultimate |
| Device application | Control |
| Aesthetic name | Flat plate |
| Product or component type | Plate switch |
| Control type | Rocker |
| Switch function | 1-pole 2-way |
| Rated current | 16 AX at 230 V AC |

Complementary

| | |
|-------------------------|-----------------|
| Connections - terminals | Screw terminals |
| Material | Stainless steel |
| Quantity per set | Set of 1 |
| Number of gangs | 4 gangs |
| Device mounting | Wall mounted |
| Height | 88 Mm |
| Width | 148 Mm |
| Depth | 24 Mm |

Environment

| | |
|-------------------------|---------------|
| Standards | BS EN 60669-1 |
| IP degree of protection | IP20 |

Offer Sustainability

| | |
|----------------------------|---|
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

| | |
|-----------------------|----------------|
| Product Life Status : | Commercialised |
|-----------------------|----------------|