



Main

Range of product	Ultimate
Range	Ultimate
Aesthetic name	Screwless flat plate
Product or component type	Plate switch
Control type	Rocker
Switch function	1-pole 2-way
Rated current	16 AX at 230 V AC

Complementary

Connections - terminals	Screw terminals
Material	Steel
Quantity per set	Set of 1
Number of gangs	3 gangs
Device mounting	Wall mounted
Height	88 Mm
Width	88 Mm
Depth	24 Mm

Environment

Standards	BS EN 60669-1
IP degree of protection	IP20

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**