

# Product data sheet

## Characteristics

# GU2214WPC

Ultimate Flat plate - 2-pole switch - 1 gang - chrome



### Main

Range of product	Ultimate
Range	Ultimate
Aesthetic name	Flat plate
Product or component type	Switch
Switch function	2-pole
Rated current	20 AX at 230 V AC

### Complementary

Connections - terminals	Screw terminals
Quantity per set	Set of 1
Number of gangs	1 gang
Pilot light	Red neon indicator
Height	88 Mm
Width	88 Mm

### Environment

Standards	BS EN 60669-1
IP degree of protection	IP20

### Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.