



### Main

Range of product	Ultimate
Range	Ultimate
Aesthetic name	Screwless flat plate
Product or component type	Switch
Switch function	2-pole
Rated current	32 A at 230 V AC

### Complementary

Connections - terminals	Screw terminals
Quantity per set	Set of 1
Number of gangs	1 gang
Pilot light	Red neon indicator
Height	88 Mm
Width	88 Mm

### Environment

Standards	BS EN 60669-1
IP degree of protection	IP20

### Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**