



Main

| | |
|---------------------------|-------------------------|
| Range of product | Ultimate |
| Range | Ultimate |
| Device application | Residential |
| Aesthetic name | Flat plate |
| Product or component type | Shaver socket |
| Input voltage | 230 V AC 50 Hz |
| Colour tint | Brass polished White |

Complementary

| | |
|-------------------------|------------------------|
| Material | Steel |
| Fixing mode | By screws M3.5 x 30 mm |
| Device mounting | Flush |
| Connections - terminals | Screw terminals |
| Quantity per set | Set of 1 |
| Height | 148 Mm |
| Width | 88 Mm |
| Depth | 47 Mm |

Environment

| | |
|-------------------------|-----------------|
| Standards | BS EN 61558-2-5 |
| IP degree of protection | IP20 |

Offer Sustainability

| | |
|----------------------------|---|
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Product Life Status : **Commercialised**