



Main

Range of product	Ultimate
Range	Ultimate
Device application	Power supply
Aesthetic name	Flat plate
Product or component type	Shaver socket
Input voltage	230 V AC 50 Hz
Colour tint	Chrome polished White

Complementary

[In] rated current	20 A
Material	Stainless steel
Fixing mode	By screws M3.5 x 30 mm
Device mounting	Flush
Connections - terminals	Screw terminals
Quantity per set	Set of 1
Height	148 Mm
Width	88 Mm
Depth	47 Mm

Environment

Standards	BS EN 61558-2-5
IP degree of protection	IP20

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------